

CTTPS_{1/2} – CRYO TIP/TILT/PISTON STAGE 1/2



Features

- Driven by Cryo Linear Actuators
- Play free
- Self locking; no power dissipation when "off"
- Materials: stainless steel, titanium
- 20 mK to 375 K, vacuum compatible
- Sub-nanometer stability
- 1/2" mounting hole (12,7 mm)
- Optics side-clamped with a spring-loaded screw
- Membrane eliminates erratic lateral motion

Description / Applications

The CTTPS_{1/2} accepts 1/2" or 12,7 mm optical elements and can be operated in a cryo-vacuum environment. It is actuated with JPE's Cryo Linear Actuators (CLA). Play of the tip / tilt / piston motion is eliminated by built-in preload springs. The optics are clamped from the side with a single spring-loaded screw.

Specifications

General info	
Type of motion	Tip / tilt / piston
Dimensions	See drawings below
Operational environmental conditions	20 mK to 375 K, ambient to UHV
Weight	160 g
Stepping motion	
Tip / tilt range	-7,2 deg to 7,2 deg
Piston range	-1,5 mm to 1,5 mm
Actuator	CLA2201
Minimal step size	μrad
Drive voltage	-30 V to 120 V
Forces and load capacity	
Mounting hole diameter	1/2" or 12,7 mm
Free aperture diameter	11,5 mm
Load capacity	100 g
Materials	
Main body	Titanium, stainless steel 316L
CLA2201	Stainless steel 316L, ceramic, piezo actuator*
*Piezo actuator	Low voltage multilayer, ceramic insulated
Electronics CPSC	
Controller Base Cabinet	CAB
Driver for stepping and scanning	CADM

CTTPS₁ – CRYO TIP/TILT/PISTON STAGE 1



Features

- Driven by Cryo Linear Actuators
- Play free
- Self locking; no power dissipation when “off”
- Materials: stainless steel, titanium
- 20 mK to 375 K, vacuum compatible
- Sub-nanometer stability
- 1” mounting hole (25,4 mm)
- Optics side-clamped with a spring-loaded screw
- Membrane eliminates erratic lateral motion

Description / Applications

The CTTPS₁ accepts 1” or 25,4 mm optical elements and can be operated in a cryo-vacuum environment. It is actuated with JPE’s Cryo Linear Actuators (CLA). Play of the tip / tilt / piston functionality is eliminated by built-in preload springs. The optics are clamped from the side with a single spring-loaded screw.

Specifications

General info	
Type of motion	Tip / tilt / piston
Dimensions	See drawings below
Operational environmental conditions	20 mK to 375 K, ambient to UHV
Weight	170 g
Stepping motion	
Tip / tilt range	-5,6 deg to 5,6 deg
Piston range	-1,5 mm to 1,5 mm
Actuator	CLA2201
Minimal step size	μrad
Drive voltage	-30 V to 120 V
Forces and load capacity	
Mounting hole diameter	1” or 25,4 mm
Free aperture diameter	21 mm
Load capacity	100 g
Materials	
Main body	Titanium, stainless steel 316L
CLA2201	Stainless steel 316L, ceramic, piezo actuator*
*Piezo actuator	Low voltage multilayer, ceramic insulated
Electronics CPSC	
Controller Base Cabinet	CAB
Driver for stepping and scanning	CADM

